

# Varistar Colocation Cabinet, RAL 9003

## Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 9003 to accommodate servers while separating access and cabling of the compartments.

### CERTIFICATIONS



### FEATURES

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 9003

### SPECIFICATIONS

**Product Type:** Rack

**Frame Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Height | Cladding Material | Frame Color | Width | Frame Color Code |
|----------------|-------------|--------|-------------------|-------------|-------|------------------|
|----------------|-------------|--------|-------------------|-------------|-------|------------------|

|           |     |        |       |              |       |          |
|-----------|-----|--------|-------|--------------|-------|----------|
| 12130-202 | 40U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-203 | 39U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-204 | 40U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-205 | 40U | 2000mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-206 | 39U | 2000mm | Steel | Black Grey   | 800mm | RAL 7021 |
| 12130-207 | 40U | 2000mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-208 | 44U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-209 | 45U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-210 | 44U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-211 | 44U | 2200mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-212 | 45U | 2200mm | Steel | Black Grey   | 800mm | RAL 7021 |
| 12130-213 | 44U | 2200mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-214 | 40U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-215 | 39U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-216 | 40U | 2000mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-217 | 40U | 2000mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-218 | 39U | 2000mm | Steel | Black Grey   | 800mm | RAL 7021 |
| 12130-219 | 40U | 2000mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-220 | 44U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |

|           |     |        |       |              |       |          |
|-----------|-----|--------|-------|--------------|-------|----------|
| 12130-221 | 45U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-222 | 44U | 2200mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-223 | 44U | 2200mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-224 | 45U | 2200mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-225 | 44U | 2200mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-257 | 45U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-258 | 48U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-259 | 48U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-260 | 45U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-261 | 48U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-262 | 48U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-269 | 45U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-270 | 48U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-271 | 48U | 2450mm | Steel | Signal White | 600mm | RAL 7021 |
| 12130-272 | 45U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-273 | 48U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |
| 12130-274 | 48U | 2450mm | Steel | Signal White | 800mm | RAL 7021 |

Table 2/3

| Catalog Number | Cladding Color | Cladding Color Code | Depth | Package Quantity | Number of Compartments | Finish |
|----------------|----------------|---------------------|-------|------------------|------------------------|--------|
|----------------|----------------|---------------------|-------|------------------|------------------------|--------|

|           |              |          |        |   |   |               |
|-----------|--------------|----------|--------|---|---|---------------|
| 12130-202 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-203 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-204 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-205 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-206 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-207 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-208 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-209 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-210 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-211 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-212 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-213 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-214 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |
| 12130-215 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-216 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |
| 12130-217 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |
| 12130-218 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-219 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |
| 12130-220 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |

|           |              |          |        |   |   |               |
|-----------|--------------|----------|--------|---|---|---------------|
| 12130-221 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-222 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |
| 12130-223 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |
| 12130-224 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-225 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |
| 12130-257 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-258 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-259 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-260 | Signal White | RAL 9003 | 1000mm | 1 | 2 | Powder Coated |
| 12130-261 | Signal White | RAL 9003 | 1000mm | 1 | 3 | Powder Coated |
| 12130-262 | Signal White | RAL 9003 | 1000mm | 1 | 4 | Powder Coated |
| 12130-269 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |
| 12130-270 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-271 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |
| 12130-272 | Signal White | RAL 9003 | 1200mm | 1 | 2 | Powder Coated |
| 12130-273 | Signal White | RAL 9003 | 1200mm | 1 | 3 | Powder Coated |
| 12130-274 | Signal White | RAL 9003 | 1200mm | 1 | 4 | Powder Coated |

| Table 3/3      |          |             |
|----------------|----------|-------------|
| Catalog Number | Material | Static Load |
| 12130-202      | Steel    | 800kg       |

| Catalog Number | Material | Static Load |
|----------------|----------|-------------|
| 12130-203      | Steel    | 800kg       |
| 12130-204      | Steel    | 800kg       |
| 12130-205      | Steel    | 800kg       |
| 12130-206      | Steel    | 800kg       |
| 12130-207      | Steel    | 800kg       |
| 12130-208      | Steel    | 800kg       |
| 12130-209      | Steel    | 800kg       |
| 12130-210      | Steel    | 800kg       |
| 12130-211      | Steel    | 800kg       |
| 12130-212      | Steel    | 800kg       |
| 12130-213      | Steel    | 800kg       |
| 12130-214      | Steel    | 800kg       |
| 12130-215      | Steel    | 800kg       |
| 12130-216      | Steel    | 800kg       |
| 12130-217      | Steel    | 800kg       |
| 12130-218      | Steel    | 800kg       |
| 12130-219      | Steel    | 800kg       |
| 12130-220      | Steel    | 800kg       |

| Catalog Number | Material | Static Load |
|----------------|----------|-------------|
| 12130-221      | Steel    | 800kg       |
| 12130-222      | Steel    | 800kg       |
| 12130-223      | Steel    | 800kg       |
| 12130-224      | Steel    | 800kg       |
| 12130-225      | Steel    | 800kg       |
| 12130-257      | Steel    | 800kg       |
| 12130-258      | Steel    | 800kg       |
| 12130-259      | Steel    | 800kg       |
| 12130-260      | Steel    | 800kg       |
| 12130-261      | Steel    | 800kg       |
| 12130-262      | Steel    | 800kg       |
| 12130-269      | Steel    | 800kg       |
| 12130-270      | Steel    | 800kg       |
| 12130-271      | Steel    | 800kg       |
| 12130-272      | Steel    | 800kg       |
| 12130-273      | Steel    | 800kg       |
| 12130-274      | Steel    | 800kg       |

## ADDITIONAL PRODUCT DETAILS

---

Side panel must be ordered separately. For suitable cable panel see Accessories.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**