


Through Roof PVC Assembly, Parallel Conductor to Parallel Conductor



CERTIFICATIONS



FEATURES

Allows for lightning protection conductors to be concealed in ceiling or walls

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/1


Catalog Number	Material	Connection Material	Rod Length (L)	Outer Diameter (OD)	Unit Weight	Certifications
LPA66424	Aluminum, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Aluminum - Aluminum	609.6mm	33.4 mm	1.56 kg	E202878-Combined_CoC, E202878-Combined_CoC

CatalogNumber	Material	Connection Material	Rod Length (L)	Outer Diameter (OD)	Unit Weight	Certifications
LPC66424	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper - Copper	609.6mm	33.4 mm	1.26 kg	
LPC664A18	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Aluminum - Copper	457.2mm	33.4 mm	1.04 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC66418	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Copper - Copper	457.2mm	33.4 mm	1.05 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPA66418	Aluminum, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Aluminum - Aluminum	457.2mm	33.4 mm	1 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPC664A24	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Aluminum - Copper	609.6mm	33.4 mm	1.21 kg	E202878-Combined_CoC, E202878-Combined_CoC

ADDITIONAL PRODUCT DETAILS

Always consult the roof manufacturer or owner for proper flashing materials.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including vinyl chloride, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE