


# Quick Release Fastener



1/4 rotary lock with defined stop.

## CERTIFICATIONS



## FEATURES

1/4 rotary lock with defined stop

Identification of locking position due to slot position

Vibration and shake proof

Qty 100 pieces

## SPECIFICATIONS

|                      |                                  |
|----------------------|----------------------------------|
| <b>Works With:</b>   | Front Panels                     |
| <b>Product Type:</b> | Hardware Kit                     |
| <b>Finish:</b>       | Nickel Plated                    |
| <b>Material:</b>     | Steel; Zinc Alloy; Thermoplastic |

Table 1/2

| Catalog Number | Color       | Package Quantity | Color Code | Depth  | Height | Width |
|----------------|-------------|------------------|------------|--------|--------|-------|
| 21101-847      | Pebble Grey | 100              | RAL 7032   | 16.7mm | 6mm    | 7mm   |

| CatalogNumber | Color       | Package Quantity | Color Code | Depth  | Height | Width |
|---------------|-------------|------------------|------------|--------|--------|-------|
| 21101-848     | Jet Black   | 100              | RAL 9005   | 16.7mm | 6mm    | 7mm   |
| 21101-849     | Pebble Grey | 100              | RAL 7032   | 20.6mm | 6mm    | 7mm   |
| 21101-850     | Jet Black   | 100              | RAL 9005   | 20.6mm | 6mm    | 7mm   |

Table 2/2

| Catalog Number | Fastener Type         | Quick Ship |
|----------------|-----------------------|------------|
| 21101-847      | Slotted Head          | No         |
| 21101-848      | Slotted Head          | No         |
| 21101-849      | Knurled, Slotted Head | No         |
| 21101-850      | Knurled, Slotted Head | No         |

## ADDITIONAL PRODUCT DETAILS

Quick-release fasteners: mounting without threaded inserts.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**