

# Varistar CP Glazed Door With 1-Point Locking

## Power Utilities

### FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Width  | Locking Type         | Color      | Color Code |
|----------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-392      | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-393      | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-481      | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-482      | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-394      | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-395      | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-483      | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-484      | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Locking Type         | Color      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-396     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-397     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-485     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-486     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-398     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-399     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-487     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-488     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-016     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-017     | 42 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-489     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-490     | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-018     | 47 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-019     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-491     | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-492     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |

Table 2/3

| Catalog Number | Complies With | Finish        | Material     | Product Type | Protection Rating | Type       |
|----------------|---------------|---------------|--------------|--------------|-------------------|------------|
| 21630-392      | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |

| CatalogNumber | Complies With | Finish        | Material     | Product Type | Protection Rating | Type       |
|---------------|---------------|---------------|--------------|--------------|-------------------|------------|
| 21630-393     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-481     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-482     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-394     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-395     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-483     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-484     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-396     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-397     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-485     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-486     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-398     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-399     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-487     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-488     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-016     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-017     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-489     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |

| CatalogNumber | Complies With | Finish        | Material     | Product Type | Protection Rating | Type       |
|---------------|---------------|---------------|--------------|--------------|-------------------|------------|
| 21630-490     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-018     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-019     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-491     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |
| 21630-492     | IEC 61587-1   | Powder Coated | Steel, Glass | Cabinet Door | IP20              | Glass Door |

Table 3/3

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-392      | Varistar CP |
| 21630-393      | Varistar CP |
| 21630-481      | Varistar CP |
| 21630-482      | Varistar CP |
| 21630-394      | Varistar CP |
| 21630-395      | Varistar CP |
| 21630-483      | Varistar CP |
| 21630-484      | Varistar CP |
| 21630-396      | Varistar CP |
| 21630-397      | Varistar CP |
| 21630-485      | Varistar CP |
| 21630-486      | Varistar CP |

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-398      | Varistar CP |
| 21630-399      | Varistar CP |
| 21630-487      | Varistar CP |
| 21630-488      | Varistar CP |
| 21630-016      | Varistar CP |
| 21630-017      | Varistar CP |
| 21630-489      | Varistar CP |
| 21630-490      | Varistar CP |
| 21630-018      | Varistar CP |
| 21630-019      | Varistar CP |
| 21630-491      | Varistar CP |
| 21630-492      | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**