We connect and protect

# CPCI Serial System With 19" PSU, Desktop, 4 U, 8 Slot, 44 HP

## CATALOG NUMBER

**24579-634**



CompactPCI Serial Desktop Chassis with vertical Card Cage nine 3 U Boards and one CompactPCI 3 U Pluggable Power Supply.

## CERTIFICATIONS

RoHS COMPLIANT

PICMG

## FEATURES

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0

System with vertical card cage. Board format Front: 3 U, 160 mm deep, 9 slot

Backplane 9 slot, 3 U, CompactPCI Serial; Power backplane

Heat dissipation by two radial fans, airflow front to rear

19" PSU, 300 W, 3 U, 8 HP

## PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 9

Type: Desktop

| |
|---|
| Backplane Type: 3 U CompactPCI Serial with Ethernet Star |
| Data Transfer: PCIe Gen3 |
| Power per Slot: 30W |
| Input Voltage AC: 100 – 240V |
| Airflow Direction: Front to Rear |
| Rack Height: 4U |
| Power Supply Type: (1) Pluggable PSU |
| Power Supply Included: Yes |
| Rear I/O: No |
| Complies With: PICMG CPCI-S.0 R2.0 |
| Depth: 275mm |
| Height: 177mm |
| Package Quantity: 1 |

## ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.


**North America**
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

**Europe**
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

**Asia**
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

**Middle East & India**
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff


Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**


©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.