

Rail Jumper Bond, Power, Compression Lugs



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Conductor insulation features low-smoke cross linked polyolefin jacket

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable

SPECIFICATIONS

Finish:	Bare;Tinned
Material:	Copper;Ethylene Propylene Rubber
Insulated:	Yes

Table 1/2


Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Width (W)	Diameter (Ø)
PBW13S01196 B	500 kcmil Ropelay	2438.4 mm	2486.4 mm	48mm	43 mm	23.42 mm
PBW13S01150 B	500 kcmil Ropelay	1270 mm	1318 mm	48mm	43 mm	23.42 mm

CatalogNumber	Conductor Size	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Width (W)	Diameter (Ø)
PBW13S01160 B	500 kcmil Ropelay	1524 mm	1572 mm	48mm	43 mm	23.42 mm
PBW13S01148 B	500 kcmil Ropelay	1219 mm	1267 mm	48mm	43 mm	23.42 mm
PBW13S01154 B	500 kcmil Ropelay	1371.6 mm	1419.6 mm	48mm	43 mm	23.42 mm

Table 2/2

Catalog Number	Hole Size (HS)	Insulation Thickness
PBW13S01196B	13 mm	2.7 mm
PBW13S01150B	13 mm	2.7 mm
PBW13S01160B	13 mm	2.7 mm
PBW13S01148B	13 mm	2.7 mm
PBW13S01154B	13 mm	2.7 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE