


# Novastar Rear Panel With Cable Ducting

## Power Utilities



Novastar Rear Panel with 3 U cable ducting for improved cable management.

## CERTIFICATIONS



## FEATURES

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Product Type       |
|----------------|-------------|---------|--------|------------|------------|--------------------|
| 25230-430      | 16 U        | 733 mm  | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-430      | 16 U        | 733 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-434      | 20 U        | 911 mm  | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-434      | 20 U        | 911 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-439      | 25 U        | 1133 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-439      | 25 U        | 1133 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-448      | 34 U        | 1534 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-448      | 34 U        | 1534 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-452      | 38 U        | 1711 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-452      | 38 U        | 1711 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-457      | 43 U        | 1933 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-457      | 43 U        | 1933 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |
| 25230-461      | 47 U        | 2111 mm | 553 mm | Black Grey | RAL 7021   | Cabinet/Rack Panel |
| 26230-461      | 47 U        | 2111 mm | 553 mm | Light Grey | RAL 7035   | Cabinet/Rack Panel |

Table 2/2

| Catalog Number | Type       |
|----------------|------------|
| 25230-430      | Rear Panel |
| 26230-430      | Rear Panel |

| Catalog Number | Type       |
|----------------|------------|
| 25230-434      | Rear Panel |
| 26230-434      | Rear Panel |
| 25230-439      | Rear Panel |
| 26230-439      | Rear Panel |
| 25230-448      | Rear Panel |
| 26230-448      | Rear Panel |
| 25230-452      | Rear Panel |
| 26230-452      | Rear Panel |
| 25230-457      | Rear Panel |
| 26230-457      | Rear Panel |
| 25230-461      | Rear Panel |
| 26230-461      | Rear Panel |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**