



# Air Terminal Base, Vertical Mount, Imperial Thread



## CERTIFICATIONS



## FEATURES

For use on vertical surfaces

Accommodates vertical or horizontal cable runs

For positive bolt tension cable clamping

## SPECIFICATIONS

**Conductor Size, UL:** Class 1 - Class 2 (4/0 Max)

Table 1/2


Catalog Number	Material	Finish	Thread Size (TS)	Hole Size (HS)	Depth (D)	Height (H)
LPA31858	Aluminum		5/8" UNC	7.14 mm	26.99mm	73.03 mm
LPA31812	Aluminum		1/2" UNC	7.14 mm	26.99mm	73.03 mm

CatalogNumber	Material	Finish	Thread Size (TS)	Hole Size (HS)	Depth (D)	Height (H)
LPC31838	Copper		3/8" UNC	7.14 mm	26.99mm	73.03 mm
LPC31858	Copper		5/8" UNC	7.14 mm	26.99mm	73.03 mm
LPC318L38	Copper	Tinned	3/8" UNC	7.14 mm	26.99mm	73.03 mm
LPC31812	Copper		1/2" UNC	7.14 mm	26.99mm	73.03 mm
LPC318L12	Copper	Tinned	1/2" UNC	7.14 mm	26.99mm	73.03 mm

Table 2/2

Catalog Number	Width (W)	Unit Weight
LPA31858	77 mm	0.13 kg
LPA31812	77 mm	0.13 kg
LPC31838	77 mm	0.38 kg
LPC31858	77 mm	0.38 kg
LPC318L38	77 mm	0.38 kg
LPC31812	77 mm	0.38 kg
LPC318L12	77 mm	0.38 kg

## DIAGRAMS



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**