nVent | SCHROFF

We connect and protect

On Board Rack 6 U, 84 HP

CATALOG NUMBER

10170-012



Suitable for ongoing vibrations, shock, high temperatures, and high humidity.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- For mobile railway applications
- Suitable for ongoing vibrations, shock, high temperatures, and high humidity
- Suitable for 1, 2, or 3 U SNCF subracks (NF F61-005, CF 60-002)
- Rear side is equipped for standard connectors; crossbar can be custom-coded for the SNCF coding pins
- Crossbar with integrated cable channel
- Several racks can be stacked or fitted in rows
- Produced using a welding process, certified to EN 15085 (CL2)
- Stainless Steel welds passivated to prevent corrosion

PRODUCT ATTRIBUTES

- Product Family: On Board Rack
- Rack Height: 6U
- Height: 290mm
- Rack Width: 84HP

Width: 496.4mm

Package Quantity: 1

Complies With: SNCF NFF 61005; SNCF NFF 60002

Depth: 341.8mm

Frame Material: Steel

Material: Stainless Steel

Product Type: Rack

Static Load: 25kg

Gross Weight: 5.9kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.