

# Rack Panel for 19-in. Racks

## Data Solutions



The Rack Panel is used to cover unused rack space in cabinets or open frame racks for a finished appearance. It can also be used for surface mounting small devices. Panels are flat with mounting slots spaced at 19-inch EIA standard spacing. Please note the mounting hardware is sold separately.

### FEATURES

The Rack Panel is used to cover unused rack space in cabinets or open frame racks for a finished appearance

It can also be used for surface mounting mall devices

Panels are flat with mounting slots spaced at 19-inch EIA standard spacing

Mounting hardware is sold separately

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|------------|---------------|-----------|------------|-----------|
| P19RPP1UB      | 13753          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |
| P19RPP2UB      | 13754          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |
| P19RPP3UB      | 13755          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |
| P19RPP4UB      | 13756          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |
| P19RPP5UB      | 13757          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |

| CatalogNumber | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|---------------|----------------|------------|---------------|-----------|------------|-----------|
| P19RPP6UB     | 13758          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 2.66mm    |

Table 2/2

| Catalog Number | Article Number | Rack Units |
|----------------|----------------|------------|
| P19RPP1UB      | 13753          | 1U         |
| P19RPP2UB      | 13754          | 2U         |
| P19RPP3UB      | 13755          | 3U         |
| P19RPP4UB      | 13756          | 4U         |
| P19RPP5UB      | 13757          | 5U         |
| P19RPP6UB      | 13758          | 6U         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**