


# Louver Plate Kit



Designed to provide ventilation in enclosures where excessive internal heat or excessive moisture is a problem. These kits may be easily installed in the field by making a cutout of the proper size and attaching the louver plate in place.

## FEATURES

---

Mounting hardware included

Custom sizes, materials, finishes, etc., can be provided on special order

## SPECIFICATIONS

| Table 1/1      |                |        |       |       |                      |               |
|----------------|----------------|--------|-------|-------|----------------------|---------------|
| Catalog Number | Article Number | Height | Width | Depth | Material             | Finish        |
| AVK23          | 24900          | 83mm   | 83mm  | 5mm   | Mild Steel           | Powder Coated |
| AVK23SS6       | 84970          | 83mm   | 83mm  | 5mm   | Stainless Steel 316L | Brushed       |
| AVK33          | 24910          | 99mm   | 114mm | 6mm   | Mild Steel           | Powder Coated |
| AVK33SS6       | 84980          | 99mm   | 114mm | 6mm   | Stainless Steel 316L | Brushed       |
| AVK34          | 24920          | 121mm  | 114mm | 6mm   | Mild Steel           | Powder Coated |
| AVK34SS6       | 84990          | 121mm  | 114mm | 6mm   | Stainless Steel 316L | Brushed       |
| AVK43SS6       | 85000          | 114mm  | 140mm | 6mm   | Stainless Steel 316L | Brushed       |
| AVK44          | 24940          | 143mm  | 140mm | 6mm   | Mild Steel           | Powder Coated |
| AVK44SS6       | 85010          | 143mm  | 140mm | 6mm   | Stainless Steel 316L | Brushed       |
| AVK64          | 24950          | 143mm  | 191mm | 8mm   | Mild Steel           | Powder Coated |
| AVK64SS6       | 85020          | 143mm  | 191mm | 8mm   | Stainless Steel 316L | Brushed       |
| AVK66          | 24960          | 200mm  | 191mm | 8mm   | Mild Steel           | Powder Coated |
| AVK66SS6       | 85030          | 200mm  | 191mm | 8mm   | Stainless Steel 316L | Brushed       |
| AVK812         | 25000          | 389mm  | 241mm | 8mm   | Mild Steel           | Powder Coated |
| AVK812SS6      | 85070          | 389mm  | 241mm | 8mm   | Stainless Steel 316L | Brushed       |
| AVK84          | 24970          | 148mm  | 241mm | 8mm   | Mild Steel           | Powder Coated |
| AVK84SS6       | 85040          | 148mm  | 241mm | 8mm   | Stainless Steel 316L | Brushed       |
| AVK86          | 24980          | 208mm  | 241mm | 8mm   | Mild Steel           | Powder Coated |
| AVK86SS6       | 85050          | 208mm  | 241mm | 8mm   | Stainless Steel 316L | Brushed       |

| Catalog Number | Article Number | Height | Width | Depth | Material                | Finish        |
|----------------|----------------|--------|-------|-------|-------------------------|---------------|
| AVK88          | 24990          | 268mm  | 241mm | 8mm   | Mild Steel              | Powder Coated |
| AVK88SS6       | 85060          | 268mm  | 241mm | 8mm   | Stainless Steel<br>316L | Brushed       |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE