

# nVent CADDY BCSP Box/Conduit Securement Platform Assembly



## **FEATURES**

Ideal single-rod securement for box/conduit installations

Accommodates a wide range of electrical boxes

Contains embedded rivet nut - no penetrating the electrical box

Tool-free securement options

# **SPECIFICATIONS**

Finish: Pregalvanized

Material: Steel

Table 1/1										
Catalog Number	Knockout Sizes	Box Depth	Box Size	Box Volume	Ground Wire Included	Rod Size				
SP45R25P1	(12) 1/2", 3/4"	2.12"	4 11/16"	42in³	Yes	1/4"				
SP45R25D5	(4) 1", 1-1/4", (1) 1/2"	2 7/8"	5"	67in³	Yes	1/4"				
SP45R254D	(4) 1/2", 3/4", (8) 1/2"	2.12"	4"	30.3in³	Yes	1/4"				
SP612RB12		4"	12"	546in³	Yes	3/8"				

CatalogNumber	Knockout Sizes	Box Depth	Box Size	Box Volume	Ground Wire Included	Rod Size
SP612RB08		3"	8"	179in³	Yes	3/8"
SP612AS12		4"	12"		Yes	3/8"
SP612AS08		4"	8"		Yes	3/8"
SP454D	(4) 1/2", 3/4", (8) 1/2"	2.12"	4"	30.3in³	Yes	3/8"
SP45P1	(12) 1/2", 3/4"	2.12"	4 11/16"	42in³	Yes	3/8"
SP45D5	(4) 1", 1-1/4", (1) 1/2"	2 7/8"	5"	67in³	Yes	3/8"

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



This document is system-generated.

Our powerful portfolio of brands:

CADDY ERI

**ERICO HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.