

# **nVent CADDY Flared Traditional Coupler**



The nVent CADDY Flared Traditional Couplers are designed to reduce the number of steps required for installing conduit racks. The integrated flare helps align each piece of conduit to easily join and install prefabricated conduit racks. This design allows the coupler to simply slide over the conduit and have visual confirmation of correct insertion depth through the center viewport. Contractors can enjoy a significantly decreased amount of ladder time for overhead installations.

#### **CERTIFICATIONS**





#### **FEATURES**

Designed for EMT conduit

Fast and simple installation

Center view slit in couplers center assists in conduit placement


Integrated flare feature is ideal for prefabrication


## **SPECIFICATIONS**

Table 1/1								
Catalog Number	Length (L)	Width (W)	Height (H)	Depth (D)	Certifications			
FC0050	1.795"	1.043"	1.499"	0.729"				
FC0075	2.185"	1.3"	1.756"	0.945"	cUL, UL			
FC0100	2.72"	1.625"	2.075"	1.185"	UL, cUL			
FC0125	3.325"	1.93"	2.39"	1.535"	cUL, UL			

Catalog Number	Length (L)	Width (W)	Height (H)	Depth (D)	Certifications
FC0150	3.872"	2.388"	2.848"	1.772"	UL, cUL
FC0200	4.187"	2.85"	3.31"	2.234"	cUL, UL
FC0250	4.828"	3.854"	4.385"	2.92"	UL, cUL
FC0300	4.999"	4.41"	4.941"	3.552"	UL, cUL
FC0350	5.479"	5.242"	5.773"	4.057"	UL, cUL
FC0400	5.675"	5.748"	6.279"	4.563"	UL, cUL

### **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

## Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

## **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO SCHROFF**  **TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.