


WBT Performance Cable Tray PreForm Tee



nVent CADDY WBT Performance Cable Tray PreForm is a cleaner, faster, more uniform engineered solution for pathway bends, tees and intersections. The PreForm Tee is a revolutionary, time-saving solution for seamless intersections ensuring clean engineering precision and effortless attachment without cutting or configuring. Due to its unique design, this offering provides up to 60% reduction in labor and time compared to traditional methods while maintaining flexibility and cost-effectiveness in tray pathway retrofits.

FEATURES

Routes cable systems in two directions

Maintains UL classification throughout installation

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/1

Catalog Number	Color	Height	Width	Length	Unit Weight
WBTT2X4		2"	12 1/2"	20.2"	0.206 lb
WBTT2X4BA	Black	2"	12 1/2"	20.2"	0.206 lb
WBTT2X4WH	White	2"	12 1/2"	20.2"	0.206 lb
WBTT2X6		2"	14.4"	22.1"	0.617 lb

Catalog Number	Color	Height	Width	Length	Unit Weight
WBTT2X6BA	Black	2"	14.4"	22.1"	0.617 lb
WBTT2X6WH	White	2"	14.4"	22.1"	0.617 lb
WBTT2X8		2"	16.4"	24.1"	0.823 lb
WBTT2X8BA	Black	2"	16.4"	24.1"	0.823 lb
WBTT2X8WH	White	2"	16.4"	24.1"	0.823 lb
WBTT2X12		2"	20.3"	28"	1.235 lb
WBTT2X12BA	Black	2"	20.3"	28"	1.235 lb
WBTT2X12WH	White	2"	20.3"	28"	1.235 lb
WBTT2X16		2"	24.3"	32"	1.646 lb
WBTT2X16BA	Black	2"	24.3"	32"	1.646 lb
WBTT2X16WH	White	2"	24.3"	32"	1.646 lb
WBTT2X18		2"	26.3"	34"	2.057 lb
WBTT2X18BA	Black	2"	26.3"	34"	2.057 lb
WBTT2X18WH	White	2"	26.3"	34"	2.057 lb
WBTT2X20BA	Black	2"	28.2"	35.9"	2.675 lb
WBTT2X20WH	White	2"	28.2"	35.9"	2.675 lb
WBTT2X24		2"	32.2"	39.9"	3.292 lb
WBTT2X24BA	Black	2"	32.2"	39.9"	3.292 lb

Catalog Number	Color	Height	Width	Length	Unit Weight
WBTT2X24WH	White	2"	32.2"	39.9"	3.292 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

