


# Cable to Cable, Heavy Duty, PT, 300 kcmil Concentric, 2/0 Concentric, Wear Plates

## Data Solutions

### CATALOG NUMBER

---

**HDPTC3A2GW**



Heavy duty connections were originally developed to be used on reclaimed cable. The heavy duty connections use a larger size connection cavity in the mold and a larger size welding material than the equivalent standard duty connection.

The larger size welding material supplies extra BTU's to melt the heavy oxide coating on the conductor and to overcome some severe field conditions. Heavy duty connections eliminate cutting the run conductor on certain types of connections, reduce cable cleaning requirements for old or reclaimed cable, and increase reliability under adverse field conditions.

Heavy duty connections are increasingly being specified for copper-coated steel conductor connections.

### CERTIFICATIONS

---



### FEATURES

---

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

PRODUCT ATTRIBUTES

|                                                      |
|------------------------------------------------------|
| Mold Family: PT Mold Family                          |
| Conductor 1: 300 kcmil Concentric                    |
| Conductor 1 Outer Diameter, Nominal: 0.63in          |
| Conductor 2: 2/0 Concentric                          |
| Conductor 2 Outer Diameter, Nominal: 0.42in          |
| Mold Split: Vertical                                 |
| Split Crucible: No                                   |
| Wear Plates: Yes                                     |
| Number of Wear Plate Sets: 2                         |
| Mold Only: No                                        |
| Welding Material: 250 or 250PLUSF20, Sold Separately |
| Handle Clamp: L160, Sold Separately                  |
| Price Key: C                                         |
| Ease of Use: Preferred                               |

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

| HD-XX-X-XX-XX-L-M-W |                        |                                                                                         |
|---------------------|------------------------|-----------------------------------------------------------------------------------------|
| HD                  | Heavy Duty Designation |                                                                                         |
| XX                  | Mold Family            |                                                                                         |
| X                   | Price Key              |                                                                                         |
| XX                  | Conductor Code 1       |                                                                                         |
| XX                  | Conductor Code 2       |                                                                                         |
| L*                  | Split Crucible         | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*                  | Mold Only              |                                                                                         |
| W*                  | Wear Plates            | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**