

# Varistar CP Cross Member for seismic frame



Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load. The hole pattern allows easy reccessment of the 19" plane in 25 mm increments.

## FEATURES

Side crossbar to support 19" uprights in a 800 mm wide reinforced cabinet supporting 800 kg static load

Hole pattern allows easy reccessment of the 19" plane in 25 mm increments

## SPECIFICATIONS

Table 1/2

| Catalog Number | Works With  | Material | Finish        | Color      | Color Code | Depth |
|----------------|-------------|----------|---------------|------------|------------|-------|
| 24630-217      | Varistar CP | Steel    | Powder Coated | Black Grey | RAL 7021   | 900mm |
| 24630-216      | Varistar CP | Steel    | Powder Coated | Black Grey | RAL 7021   | 800mm |
| 24630-215      | Varistar CP | Steel    | Powder Coated | Black Grey | RAL 7021   | 600mm |

Table 2/2

| Catalog Number | Package Quantity | Package Unit | Quick Ship |
|----------------|------------------|--------------|------------|
| 24630-217      | 4                | Pair         | No         |
| 24630-216      | 4                | Pair         | No         |
| 24630-215      | 4                | Pair         | No         |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**