

nVent CADDY Speed Link SLK with Threaded Stud End



CERTIFICATIONS





FEATURES

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

SPECIFICATIONS

Static Load Safety Factor: 5:

Finish: Electrogalvanized

Material: Steel;Polypropylene;Zinc Alloy


Complies With: SMACNA HVAC-DCS

Table 1/2							
Catalog Number	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Height (H)	Width (W)	
SLK15L2SE250	1.5 mm	6.6'	1/4"	1"	2.15"	3/4"	

CatalogNumber	Wire Rope Diameter	Wire Rope Length	Rod Size (RS)	Screw Length (L)	Height (H)	Width (W)
SLK15L3SE250	1.5 mm	9.9'	1/4"	1"	2.15"	3/4"
SLK2L3SE375	2 mm	9.9'	3/8"	1 3/4"	2.15"	3/4"
SLK2L5SE375	2 mm	16.4'	3/8"	1 3/4"	2.15"	3/4"
SLK3L3SE375	3 mm	9.9'	3/8"	1 3/4"	2 1/2"	0.9"

Table 2/2							
Catalog Number	Thickness (T)	Angle (a)	Static Load (F)	Certifications			
SLK15L2SE250	1/2"	90 ° Max	44lbf	UL, cUL			
SLK15L3SE250	1/2"	90 ° Max	44lbf	cUL, UL			
SLK2L3SE375	1/2"	90 ° Max	100lbf	UL, cUL			
SLK2L5SE375	1/2"	90 ° Max	100lbf	cUL, UL			
SLK3L3SE375	0.6"	90 ° Max	200lbf				

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.