

# Varistar CP Steel Door, Plain With 1-Point Locking

## Data Solutions



Varistar CP Steel Door, IP 20 with Single Point Locking.

### FEATURES

Steel door with single point locking for IP 20 protection class

Opening angle 180°

### SPECIFICATIONS

**Product Type:** Cabinet Door

**Protection Rating:** IP20

**Material:** Steel

Table 1/2

Catalog Number	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-002	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-003	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-004	52U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-009	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-010	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-011	52U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-400	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-401	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-402	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-403	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-404	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-405	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-406	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-407	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-493	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-494	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-495	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-496	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-497	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-498	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-499	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-500	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-501	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-502	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-503	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-504	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

Table 2/2

Catalog Number	Finish	Type	Works With
21630-002	Powder Coated	Steel Door	Varistar CP
21630-003	Powder Coated	Steel Door	Varistar CP
21630-004	Powder Coated	Steel Door	Varistar CP
21630-009	Powder Coated	Steel Door	Varistar CP
21630-010	Powder Coated	Steel Door	Varistar CP
21630-011	Powder Coated	Steel Door	Varistar CP
21630-400	Powder Coated	Steel Door	Varistar CP
21630-401	Powder Coated	Steel Door	Varistar CP
21630-402	Powder Coated	Steel Door	Varistar CP
21630-403	Powder Coated	Steel Door	Varistar CP
21630-404	Powder Coated	Steel Door	Varistar CP
21630-405	Powder Coated	Steel Door	Varistar CP
21630-406	Powder Coated	Steel Door	Varistar CP

Catalog Number	Finish	Type	Works With
21630-407	Powder Coated	Steel Door	Varistar CP
21630-493	Powder Coated	Steel Door	Varistar CP
21630-494	Powder Coated	Steel Door	Varistar CP
21630-495	Powder Coated	Steel Door	Varistar CP
21630-496	Powder Coated	Steel Door	Varistar CP
21630-497	Powder Coated	Steel Door	Varistar CP
21630-498	Powder Coated	Steel Door	Varistar CP
21630-499	Powder Coated	Steel Door	Varistar CP
21630-500	Powder Coated	Steel Door	Varistar CP
21630-501	Powder Coated	Steel Door	Varistar CP
21630-502	Powder Coated	Steel Door	Varistar CP
21630-503	Powder Coated	Steel Door	Varistar CP
21630-504	Powder Coated	Steel Door	Varistar CP

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**