

Varistar CP Steel Door, Plain With 3-Point Locking, IP20

Data Solutions



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection.

FEATURES

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Locking Type:	3-Point Locking
Product Type:	Cabinet Door
Protection Rating:	IP20
Material:	Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-104	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-105	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-106	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-107	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-108	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-109	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-432	24U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-433	24U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-434	29U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-435	29U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-436	33U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-437	33U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-438	38U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated
21630-439	38U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated

Table 2/2

Catalog Number	Type	Works With
21630-104	Steel Door	Varistar CP
21630-105	Steel Door	Varistar CP
21630-106	Steel Door	Varistar CP
21630-107	Steel Door	Varistar CP
21630-108	Steel Door	Varistar CP

Catalog Number	Type	Works With
21630-109	Steel Door	Varistar CP
21630-432	Steel Door	Varistar CP
21630-433	Steel Door	Varistar CP
21630-434	Steel Door	Varistar CP
21630-435	Steel Door	Varistar CP
21630-436	Steel Door	Varistar CP
21630-437	Steel Door	Varistar CP
21630-438	Steel Door	Varistar CP
21630-439	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE