

WBT Performance Cable Tray L Bracket



The nVent CADDY WBT Performance Cable Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY WBT Performance Cable Tray Washer Support and nVent CADDY WBT Performance Cable Tray Ground Splice

Utilize with the nVent CADDY WBT Performance Cable Tray C Bracket for multi-tier cable tray runs

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/1

Catalog Number	Color	Height	Width	Length	Hole Size	Unit Weight
WBTLBRKT12		5"	12"	14.173"	0.282"	0.288 lb
WBTLBRKT12B A	Black	5"	12"	14.173"	0.282"	0.288 lb
WBTLBRKT12W H	White	5"	12"	14.173"	0.282"	0.288 lb

CatalogNumber	Color	Height	Width	Length	Hole Size	Unit Weight
WBTBKRKT4		5"	4"	14.173"	0.282"	0.288 lb
WBTBKRKT4BA	Black	5"	4"	14.173"	0.282"	0.288 lb
WBTBKRKT4W H	White	5"	4"	14.173"	0.282"	0.288 lb
WBTBKRKT6		5"	6"	14.173"	0.282"	0.288 lb
WBTBKRKT6BA	Black	5"	6"	14.173"	0.282"	0.288 lb
WBTBKRKT6W H	White	5"	6"	14.173"	0.282"	0.288 lb
WBTBKRKT8		5"	8"	14.173"	0.282"	0.288 lb
WBTBKRKT8BA	Black	5"	8"	14.173"	0.282"	0.288 lb
WBTBKRKT8W H	White	5"	8"	14.173"	0.282"	0.288 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

