

# **WBT Performance Cable Tray Polymer Insert**



The nVent CADDY WBT Performance Cable Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray-providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

#### **FEATURES**

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection

#### **SPECIFICATIONS**


**Finish:** N/A **Material:** Polymer

Table 1/1							
Catalog Number	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Sides Included	
WBTFORM04BA	Black		3.63"	120"	0.009 lb	No	
WBTFORM06BA	Black		5.63"	120"	0.014 lb	No	
WBTFORM08BA	Black		7.63"	120"	0.018 lb	No	
WBTFORM2X4B A	Black	2"	3.63"	120"	0.018 lb	Yes	

CatalogNumber	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Sides Included
WBTFORM2X6B A	Black	2"	5.63"	120"	0.023 lb	Yes
WBTFORM12BA	Black		11.63"	120"	0.027 lb	No
WBTFORM2X8B A	Black	2"	7.63"	120"	0.027 lb	Yes
WBTFORM4X4B A	Black	4"	3.63"	120"	0.027 lb	Yes
WBTFORM4X6B A	Black	4"	5.63"	120"	0.032 lb	Yes
WBTFORM16BA	Black		15.63"	120"	0.036 lb	No
WBTFORM2X12 BA	Black	2"	11.63"	120"	0.036 lb	Yes
WBTFORM4X8B A	Black	4"	7.63"	120"	0.036 lb	Yes
WBTFORM18BA	Black		17.63"	120"	0.041 lb	No
WBTFORM20BA	Black		19.63"	120"	0.045 lb	No
WBTFORM2X16 BA	Black	2"	15.63"	120"	0.045 lb	Yes
WBTFORM4X12 BA	Black	4"	11.63"	120"	0.045 lb	Yes
WBTFORM6X8B A	Black	6"	7.63"	120"	0.045 lb	Yes
WBTFORM2X18 BA	Black	2"	17.63"	120"	0.05 lb	Yes
WBTFORM24BA	Black		23.63"	120"	0.054 lb	No

CatalogNumber	Color	Height (H)	Width (W)	Length (L)	Unit Weight	Sides Included
WBTFORM2X20 BA	Black	2"	19.63"	120"	0.054 lb	Yes
WBTFORM4X16 BA	Black	4"	15.63"	120"	0.054 lb	Yes
WBTFORM6X12 BA	Black	6"	11.63"	120"	0.054 lb	Yes
WBTFORM4X18 BA	Black	4"	17.63"	120"	0.059 lb	Yes
WBTFORM2X24 BA	Black	2"	23.63"	120"	0.064 lb	Yes
WBTFORM4X20 BA	Black	4"	19.63"	120"	0.064 lb	Yes
WBTFORM6X16 BA	Black	6"	15.63"	120"	0.064 lb	Yes
WBTFORM4X24 BA	Black	4"	23.63"	120"	0.073 lb	Yes
WBTFORM6X18 BA	Black	6"	17.63"	120"	0.073 lb	Yes
WBTFORM6X20 BA	Black	6"	19.63"	120"	0.082 lb	Yes
WBTFORM6X24 BA	Black	6"	23.63"	120"	0.082 lb	Yes

## DIAGRAMS



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

## APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.