

WBT Performance Cable Tray PreForm Intersection







nVent CADDY WBT Performance Cable Tray PreForm is a cleaner, faster and more uniform engineered solution for pathway bends, tees and intersections. The PreForm is a revolutionary, time-saving solution for seamless intersections, ensuring clean engineering, precision with effortless attachment and no cutting or configuring required. This product offers up to 60% reduction in labor and time compared to traditional methods due to the ability to maintain flexibility and cost-effectiveness in any tray pathway retrofit.

CERTIFICATIONS





FEATURES

Labor savings up to 60%

Maintains UL classification throughout installation

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/1									
Catalog Number	Color	Height	Width	Length	Unit Weight	Certifications			

WBTI2X4		2"	20.12"	20.12"	0.411 lb	cUL, UL
WBTI2X4BA	Black	2"	20.12"	20.12"	0.411 lb	
WBTI2X4WH	White	2"	20.12"	20.12"	0.411 lb	
WBTI2X6		2"	22.1"	22.1"	0.617 lb	UL, cUL
WBTI2X6BA	Black	2"	22.1"	22.1"	0.617 lb	
WBTI2X8		2"	24.1"	24.1"	1.029 lb	cUL, UL
WBTI2X8BA	Black	2"	24.1"	24.1"	1.029 lb	
WBTI2X8WH	White	2"	24.1"	24.1"	1.029 lb	
WBTI2X12		2"	28"	28"	1.44 lb	UL, cUL
WBTI2X12BA	Black	2"	28"	28"	1.44 lb	
WBTI2X12WH	White	2"	28"	28"	1.44 lb	
WBTI2X16BA	Black	2"	32"	32"	2.057 lb	
WBTI2X18		2"	33.9"	33.9"	2.469 lb	UL, cUL
WBTI2X18BA	Black	2"	33.9"	33.9"	2.469 lb	
WBTI2X20		2"	35.9"	35.9"	2.88 lb	cUL, UL
WBTI2X20BA	Black	2"	35.9"	35.9"	2.88 lb	
WBTI2X24		2"	40"	40"	3.704 lb	UL, cUL
WBTI2X24BA	Black	2"	40"	40"	3.704 lb	
WBTI2X24WH	White	2"	40"	40"	3.704 lb	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

