


Air Terminal, Metric Thread



CERTIFICATIONS



FEATURES

Lightning strike termination points for use with air terminal bases

Includes nut for securing to air terminal base

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Thread Size (TS)	Diameter (Ø)	Height (H)	Unit Weight	Complies With
LPAAR0510	Aluminum	M10	7/16"	19.68"	0.42 lb	
LPAAR0515	Aluminum	M16	5/8"	19.68"	0.58 lb	
LPAAR1010	Aluminum	M10	7/16"	39.37"	0.85 lb	
LPCAR1010	Copper	M10	7/16"	39.37"	2.42 lb	IEC® EN 62561-2

CatalogNumber	Material	Thread Size (TS)	Diameter (Ø)	Height (H)	Unit Weight	Complies With
LPCAR0510	Copper	M10	7/16"	19.68"	1.06 lb	IEC® EN 62561-2
LPCAR0515	Copper	M16	0.59"	19.68"	1.62 lb	IEC® EN 62561-2, EN IEC 62561-2:2018
LPAAR1015	Aluminum	M16	5/8"	39.37"	1.17 lb	
LPCAR1015	Copper	M16	0.59"	39.37"	3.36 lb	IEC® EN 62561-2, EN IEC 62561-2:2018
LPCAR2015	Copper	M16	0.59"	78.74"	6.85 lb	IEC® EN 62561-2, EN IEC 62561-2:2018
LPSSAR1015	Stainless Steel 304 (EN 1.4301)	M16	5/8"	39.37"	3.53 lb	


Table 2/2

Catalog Number	Certifications
LPAAR0510	
LPAAR0515	E202878-Combined_CoC, E202878-Combined_CoC
LPAAR1010	
LPCAR1010	E202878-Combined_CoC, E202878-Combined_CoC
LPCAR0510	E202878-Combined_CoC, E202878-Combined_CoC
LPCAR0515	E202878-Combined_CoC, E202878-Combined_CoC
LPAAR1015	E202878-Combined_CoC, E202878-Combined_CoC
LPCAR1015	E202878-Combined_CoC, E202878-Combined_CoC
LPCAR2015	E202878-Combined_CoC, E202878-Combined_CoC
LPSSAR1015	E202878-Combined_CoC, E202878-Combined_CoC

ADDITIONAL PRODUCT DETAILS

Multiple Point Terminal, Metric Thread (CMP163) can be used on the top of tapered Air Terminals (M16 Thread Size parts, that are made of copper).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE