

Cast Bonding Lug



CERTIFICATIONS



FEATURES

Provides contact area for main sized bonding

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max);Secondary

Table 1/2


Catalog Number	Material	Finish	Hole Size (HS)	Contact Area	Depth (D)	Height (H)
LPA55112	Aluminum	Bare	9/16"	3 in ² Min	1 9/16"	1"
LPA55114	Aluminum	Bare	5/16"	3 in ² Min	1 9/16"	1"
LPA55138	Aluminum	Bare	7/16"	3 in ² Min	1 9/16"	1"
LPC55112	Brass	Bare	9/16"	3 in ² Min	1 9/16"	1"

CatalogNumber	Material	Finish	Hole Size (HS)	Contact Area	Depth (D)	Height (H)
LPC55114	Brass	Bare	5/16"	3 in ² Min	1 9/16"	1"
LPC55138	Brass	Bare	7/16"	3 in ² Min	1 9/16"	1"
LPC551L12	Brass	Tinned	9/16"	3 in ² Min	1 9/16"	1"
LPC551L38	Brass	Tinned	7/16"	3 in ² Min	1 9/16"	1"

Table 2/2

Catalog Number	Width (W)	Unit Weight	Certifications
LPA55112	3 7/8"	0.19 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPA55114	3 7/8"	0.19 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPA55138	3 7/8"	0.19 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPC55112	3 7/8"	0.54 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPC55114	3 7/8"	0.54 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPC55138	3 7/8"	0.54 lb	E202878-Combined_CoC, E202878-Combined_CoC
LPC551L12	3 7/8"	0.54 lb	
LPC551L38	3 7/8"	0.54 lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY	ERICO	HOFFMAN	ILSCO	SCHROFF	TRACHTE
-------	-------	---------	-------	---------	---------