

Perimeter Grounding Busbar for Walls



CERTIFICATIONS





FEATURES

Perimeter grounding busbars are used to terminate ground wires and cables from equipment and other devices

For busbars that include insulators and brackets, four individual brackets and insulators are provided


SPECIFICATIONS

Table 1/2							
Catalog Number	Material	Busbar Configuration	Length (L)	Width (W)	Thickness (T)	A	
EPGC182120	Copper	Busbar Only	120"	2"	1/8"	15"	
EPGC184120	Copper	Busbar Only	120"	4"	1/8"	15"	
EPGA142120	Copper, Polyamide, Stainless Steel 304 (EN 1.4301)	Busbar, Insulators and Brackets	120"	2"	1/4"	15"	

CatalogNumber	Material	Busbar Configuration	Length (L)	Width (W)	Thickness (T)	A
EPGA144120	Copper, Polyamide, Stainless Steel 304 (EN 1.4301)	Busbar, Insulators and Brackets	120"	4"	1/4"	15"
EPGC141120	Copper	Busbar Only	120"	1"	1/4"	15"
EPGC142120	Copper	Busbar Only	120"	2"	1/4"	15"
EPGC143120	Copper	Busbar Only	120"	3"	1/4"	15"
EPGC144120	Copper	Busbar Only	120"	4"	1/4"	15"

Table 2/2						
Catalog Number	В	Hole Size (HS)				
EPGC182120	30"	7/16"				
EPGC184120	30"	7/16"				
EPGA142120	30"	7/16"				
EPGA144120	30"	7/16"				
EPGC141120	30"	7/16"				
EPGC142120	30"	7/16"				
EPGC143120	30"	7/16"				
EPGC144120	30"	7/16"				

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 $^{\Delta}$ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE