

High-Performance Pagoda Exhaust Vent Top with Cutout



The tops fit standard frames. Single-bay tops have a cutout that accepts one high-performance pagoda vent. Double-bay tops have one cutout that can be oriented for left-bay or right-bay pagoda ventilation. EMC tops are finished with paint over plated surfaces. Bolts are furnished to hold top in position.

INDUSTRY STANDARDS

This component is rated UL Type 1. Installing this component on an enclosure brings the enclosure rating to UL Type 1.

FEATURES

Top is gasketed and include ground studs.

Lifting eyes can be used in place of bolts

SPECIFICATIONS

Thickness: 16ga
Color: Light Gray
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Finish	Quick Ship
PPTHP66	24189	Mild Steel	Powder Coated	No
PPTHP68	24199	Mild Steel	Powder Coated	No
PPTHP88	24259	Mild Steel	Powder Coated	No
PPTHP86	24249	Mild Steel	Powder Coated	No
PPTHP106	24289	Mild Steel	Powder Coated	No
PPTHP108	24299	Mild Steel	Powder Coated	No
PPTHP65	24179	Mild Steel	Powder Coated	No
PPTHP76	24209	Mild Steel	Powder Coated	No
PPTHP105EMC	24489	Mild Steel	Galvanized, Powder Coated	No
PPTHP106EMC	24499	Mild Steel	Galvanized, Powder Coated	No
PPTHP108EMC	24509	Mild Steel	Galvanized, Powder Coated	No
PPTHP125EMC	24519	Mild Steel	Galvanized, Powder Coated	No
PPTHP126	24319	Mild Steel	Powder Coated	No
PPTHP126EMC	24529	Mild Steel	Galvanized, Powder Coated	No
PPTHP128	24329	Mild Steel	Powder Coated	No
PPTHP128EMC	24539	Mild Steel	Galvanized, Powder Coated	No
PPTHP165	24339	Mild Steel	Powder Coated	No

Catalog Number	Article Number	Material	Finish	Quick Ship
PPTHP165EMC	24549	Mild Steel	Galvanized, Powder Coated	No
PPTHP166	24349	Mild Steel	Powder Coated	No
PPTHP166EMC	24559	Mild Steel	Galvanized, Powder Coated	No
PPTHP168EMC	24569	Mild Steel	Galvanized, Powder Coated	No
PPTHP65EMC	24389	Mild Steel	Galvanized, Powder Coated	No
PPTHP66EMC	24399	Mild Steel	Galvanized, Powder Coated	No
PPTHP76EMC	24419	Mild Steel	Galvanized, Powder Coated	No
PPTHP78EMC	24429	Mild Steel	Galvanized, Powder Coated	No
PPTHP79EMC	24439	Mild Steel	Galvanized, Powder Coated	No
PPTHP85EMC	24449	Mild Steel	Galvanized, Powder Coated	No
PPTHP86EMC	24459	Mild Steel	Galvanized, Powder Coated	No
PPTHP88EMC	24469	Mild Steel	Galvanized, Powder Coated	No
PPTHP89EMC	24479	Mild Steel	Galvanized, Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE