

# ProLine Overlapping Doors



ProLine Overlapping Doors provide a door system for the full-width open front of 800,1000, 1200- and 1600-mm wide frames. The Primary door ensures a dust-tight seal using a 3-point roller latch system operated by a ProLine flush swing handle.

## FEATURES

overlapping primary/adjacent door design allows unobstructed access

Furnished with a ProLine flush swing handle

Removable door bar is included on each door

Primary door is hinged on the right side

## SPECIFICATIONS

**Thickness:** 14ga

Table 1/1

Catalog Number	Article Number	Material	Dimensions	Color	Color Code	Finish
PTOD1212	29825	Mild Steel	44.84 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD1412	29826	Mild Steel	52.72 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD148	19764	Mild Steel	52.72 x 31.18in	Light Gray	RAL 7035	Powder Coated
PTOD1612	19775	Mild Steel	60.59 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD168	19765	Mild Steel	60.59 x 31.18in	Light Gray	RAL 7035	Powder Coated
PTOD1810	19767	Mild Steel	68.46 x 39.06in	Light Gray	RAL 7035	Powder Coated
PTOD1812	19776	Mild Steel	68.46 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD1816	19783	Mild Steel	68.46 x 62.64in	Light Gray	RAL 7035	Powder Coated
PTOD1818	29827	Mild Steel	68.46 x 70.51in	Light Gray	RAL 7035	Powder Coated
PTOD188	19766	Mild Steel	68.46 x 31.18in	Light Gray	RAL 7035	Powder Coated
PTOD2010	19771	Mild Steel	76.34 x 39.06in	Light Gray	RAL 7035	Powder Coated
PTOD2012	19777	Mild Steel	76.34 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD2012SS	19778	Stainless Steel 304	76.34 x 46.89in			Brushed
PTOD2016	19784	Mild Steel	76.34 x 62.64in	Light Gray	RAL 7035	Powder Coated
PTOD2018	29828	Mild Steel	76.34 x 70.51in	Light Gray	RAL 7035	Powder Coated
PTOD208	19768	Mild Steel	76.34 x 31.18in	Light Gray	RAL 7035	Powder Coated
PTOD2210	19773	Mild Steel	84.21 x 39.06in	Light Gray	RAL 7035	Powder Coated
PTOD2212	19782	Mild Steel	84.21 x 46.89in	Light Gray	RAL 7035	Powder Coated

Catalog Number	Article Number	Material	Dimensions	Color	Color Code	Finish
PTOD2212SS	19781	Stainless Steel 304	84.21 x 46.89in			Brushed
PTOD228	19772	Mild Steel	84.21 x 31.18in	Light Gray	RAL 7035	Powder Coated
PTOD712	19774	Mild Steel	25.16 x 46.89in	Light Gray	RAL 7035	Powder Coated
PTOD78	19763	Mild Steel	25.16 x 31.18in	Light Gray	RAL 7035	Powder Coated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE