


Rack Panels



Rack Panels mount to rack angles and can be used for mounting components or as a blanking plate. All panels are flat with oblong holes positioned at EIA standard spacing. Mounting hardware is sold separately. The recommended fastener package kit is ECNSM6.

FEATURES

Available in aluminum or painted steel; steel is RAL 7035 textured light-gray polyester powder paint

Aluminum panels are 0.125-in. thick 5052-H32 alloy; steel panels are 12 gauge

All panels are flat with oblong holes positioned at EIA standard spacing (rack units)

Mounting hardware sold separately; recommend use of ECNSM6

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Rack Width	Rack Units	Color	Color Code
P19RP1UA	77020	Aluminum	19in	1U		
P19RP5UA	77060	Aluminum	19in	5U		
P19RP3UA	77040	Aluminum	19in	3U		
P19RP7UA	77080	Aluminum	19in	7U		
P19RP4UA	77050	Aluminum	19in	4U		
P19RP12UA	77130	Aluminum	19in	12U		
P19RP11UA	77120	Aluminum	19in	11U		
P19RP6UA	77070	Aluminum	19in	6U		
P19RP2UA	77030	Aluminum	19in	2U		
P19RP8UA	77090	Aluminum	19in	8U		
P19RP9UA	77100	Aluminum	19in	9U		
P19RP10UA	77110	Aluminum	19in	10U		
P24RP8UA	77010	Aluminum	24in	8U		
P24RP4UA	76980	Aluminum	24in	4U		
P24RP2UA	76960	Aluminum	23in	2U		
P24RP5UA	76990	Aluminum				
P19RP16UA	77140	Aluminum	19in	16U		
P23RP1UA	76900	Aluminum	23in	1U		
P23RP3UA	76920	Aluminum	23in	3U		

Catalog Number	Article Number	Material	Rack Width	Rack Units	Color	Color Code
P23RP4UA	76930	Aluminum	23in	4U		
P19RP1UP	76710	Mild Steel	19in	1U	Light Gray	RAL 7035
P23RP1UP	76590	Mild Steel	23in	1U	Light Gray	RAL 7035
P19RP2UP	76720	Mild Steel	19in	2U	Light Gray	RAL 7035
P24RP2UP	76650	Mild Steel	23in	2U	Light Gray	RAL 7035
P23RP2UP	76600	Mild Steel	23in	2U	Light Gray	RAL 7035
P19RP3UP	76730	Mild Steel	19in	3U	Light Gray	RAL 7035
P19RP4UP	76740	Mild Steel	19in	4U	Light Gray	RAL 7035
P19RP5UP	76750	Mild Steel	19in	5U	Light Gray	RAL 7035
P19RP6UP	76760	Mild Steel	19in	6U	Light Gray	RAL 7035
P19RP8UP	76780	Mild Steel	19in	8U	Light Gray	RAL 7035
P19RP7UP	76770	Mild Steel	19in	7U	Light Gray	RAL 7035
P19RP9UP	76790	Mild Steel	19in	9U	Light Gray	RAL 7035
P19RP10UP	76800	Mild Steel	19in	10U	Light Gray	RAL 7035
P19RP16UP	76830	Mild Steel	19in	16U	Light Gray	RAL 7035
P19RP12UP	76820	Mild Steel	19in	12U	Light Gray	RAL 7035
P19RP11UP	76810	Mild Steel	19in	11U	Light Gray	RAL 7035
P24RP5UP	76680	Mild Steel			Light Gray	RAL 7035
P24RP3UP	76660	Mild Steel	23in	3U	Light Gray	RAL 7035
P24RP8UP	76700	Mild Steel	24in	8U	Light Gray	RAL 7035

Catalog Number	Article Number	Material	Rack Width	Rack Units	Color	Color Code
P24RP6UP	76690	Mild Steel	24in	6U	Light Gray	RAL 7035
P24RP4UP	76670	Mild Steel	24in	4U	Light Gray	RAL 7035
P23RP3UP	76610	Mild Steel	23in	3U	Light Gray	RAL 7035
P23RP4UP	76620	Mild Steel	23in	4U	Light Gray	RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE