

Varistar CP Frame

Data Solutions



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFICATIONS

Product Type: Cabinet/Rack Frame

Material: Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Complies With	Frame Material
20630-128	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-261	42U	1	Black Grey	RAL 7021		Steel
20630-262	47U	1	Black Grey	RAL 7021		Steel
20630-127	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Frame Material
20630-065	24U	1	Black Grey	RAL 7021		Steel
20630-066	24U	1	Black Grey	RAL 7021		Steel
20630-067	24U	1	Black Grey	RAL 7021		Steel
20630-068	24U	1	Black Grey	RAL 7021		Steel
20630-071	24U	1	Black Grey	RAL 7021		Steel
20630-072	24U	1	Black Grey	RAL 7021		Steel
20630-073	24U	1	Black Grey	RAL 7021		Steel
20630-074	24U	1	Black Grey	RAL 7021		Steel
20630-075	29U	1	Black Grey	RAL 7021		Steel
20630-076	29U	1	Black Grey	RAL 7021		Steel
20630-077	29U	1	Black Grey	RAL 7021		Steel
20630-078	29U	1	Black Grey	RAL 7021		Steel
20630-079	29U	1	Black Grey	RAL 7021		Steel
20630-080	29U	1	Black Grey	RAL 7021		Steel
20630-081	29U	1	Black Grey	RAL 7021		Steel
20630-082	29U	1	Black Grey	RAL 7021		Steel
20630-083	33U	1	Black Grey	RAL 7021		Steel
20630-084	33U	1	Black Grey	RAL 7021		Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Frame Material
20630-085	33U	1	Black Grey	RAL 7021		Steel
20630-086	33U	1	Black Grey	RAL 7021		Steel
20630-087	33U	1	Black Grey	RAL 7021		Steel
20630-088	33U	1	Black Grey	RAL 7021		Steel
20630-089	33U	1	Black Grey	RAL 7021		Steel
20630-090	33U	1	Black Grey	RAL 7021		Steel
20630-091	38U	1	Black Grey	RAL 7021		Steel
20630-092	38U	1	Black Grey	RAL 7021		Steel
20630-093	38U	1	Black Grey	RAL 7021		Steel
20630-094	38U	1	Black Grey	RAL 7021		Steel
20630-095	38U	1	Black Grey	RAL 7021		Steel
20630-096	38U	1	Black Grey	RAL 7021		Steel
20630-097	38U	1	Black Grey	RAL 7021		Steel
20630-098	38U	1	Black Grey	RAL 7021		Steel
20630-099	42U	1	Black Grey	RAL 7021		Steel
20630-100	42U	1	Black Grey	RAL 7021		Steel
20630-101	42U	1	Black Grey	RAL 7021		Steel
20630-102	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Frame Material
20630-103	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-104	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-105	42U	1	Black Grey	RAL 7021		Steel
20630-106	42U	1	Black Grey	RAL 7021		Steel
20630-107	42U	1	Black Grey	RAL 7021		Steel
20630-108	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-109	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-110	42U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-111	47U	1	Black Grey	RAL 7021		Steel
20630-112	47U	1	Black Grey	RAL 7021		Steel
20630-113	47U	1	Black Grey	RAL 7021		Steel
20630-114	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-115	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-116	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-117	47U	1	Black Grey	RAL 7021		Steel
20630-118	47U	1	Black Grey	RAL 7021		Steel
20630-119	47U	1	Black Grey	RAL 7021		Steel
20630-120	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Frame Material
20630-121	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-122	47U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-123	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-124	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-125	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel
20630-126	52U	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Steel

Table 2/2

Catalog Number	Type	Works With
20630-128	Standard	Varistar CP
20630-261	Standard	Varistar CP
20630-262	Standard	Varistar CP
20630-127	Standard	Varistar CP
20630-065	Standard	Varistar CP
20630-066	Standard	Varistar CP
20630-067	Standard	Varistar CP
20630-068	Standard	Varistar CP
20630-071	Standard	Varistar CP
20630-072	Standard	Varistar CP
20630-073	Standard	Varistar CP

Catalog Number	Type	Works With
20630-074	Standard	Varistar CP
20630-075	Standard	Varistar CP
20630-076	Standard	Varistar CP
20630-077	Standard	Varistar CP
20630-078	Standard	Varistar CP
20630-079	Standard	Varistar CP
20630-080	Standard	Varistar CP
20630-081	Standard	Varistar CP
20630-082	Standard	Varistar CP
20630-083	Standard	Varistar CP
20630-084	Standard	Varistar CP
20630-085	Standard	Varistar CP
20630-086	Standard	Varistar CP
20630-087	Standard	Varistar CP
20630-088	Standard	Varistar CP
20630-089	Standard	Varistar CP
20630-090	Standard	Varistar CP
20630-091	Standard	Varistar CP

Catalog Number	Type	Works With
20630-092	Standard	Varistar CP
20630-093	Standard	Varistar CP
20630-094	Standard	Varistar CP
20630-095	Standard	Varistar CP
20630-096	Standard	Varistar CP
20630-097	Standard	Varistar CP
20630-098	Standard	Varistar CP
20630-099	Standard	Varistar CP
20630-100	Standard	Varistar CP
20630-101	Standard	Varistar CP
20630-102	Standard	Varistar CP
20630-103	Standard	Varistar CP
20630-104	Standard	Varistar CP
20630-105	Standard	Varistar CP
20630-106	Standard	Varistar CP
20630-107	Standard	Varistar CP
20630-108	Standard	Varistar CP
20630-109	Standard	Varistar CP

Catalog Number	Type	Works With
20630-110	Standard	Varistar CP
20630-111	Standard	Varistar CP
20630-112	Standard	Varistar CP
20630-113	Standard	Varistar CP
20630-114	Standard	Varistar CP
20630-115	Standard	Varistar CP
20630-116	Standard	Varistar CP
20630-117	Standard	Varistar CP
20630-118	Standard	Varistar CP
20630-119	Standard	Varistar CP
20630-120	Standard	Varistar CP
20630-121	Standard	Varistar CP
20630-122	Standard	Varistar CP
20630-123	Standard	Varistar CP
20630-124	Standard	Varistar CP
20630-125	Standard	Varistar CP
20630-126	Standard	Varistar CP

ADDITIONAL PRODUCT DETAILS

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE