

## Window Door, ADT



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

### FEATURES

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 3 mm transparent acrylic glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP55, IK 07.

Pack quantity: 1 door.

## SPECIFICATIONS

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Latch Quantity
ADT03025R5	ADT03025R5	11.61in	9.65in	0.61in	18ga	1
ADT03030R5	ADT03030R5	11.61in	11.61in	0.61in	18ga	1
ADT04030R5	ADT04030R5	15.55in	11.61in	0.61in	18ga	1
ADT04040R5	ADT04040R5	15.55in	15.55in	0.61in	18ga	1
ADT05030R5	ADT05030R5	19.49in	11.61in	0.61in	16ga	1
ADT05040R5	ADT05040R5	19.49in	15.55in	0.61in	16ga	1
ADT06040R5	ADT06040R5	23.43in	15.55in	0.61in	16ga	2
ADT06050R5	ADT06050R5	23.43in	19.49in	0.61in	16ga	2
ADT06060R5	ADT06060R5	23.43in	23.43in	0.61in	16ga	2
ADT07050R5	ADT07050R5	27.36in	19.49in	0.61in	16ga	2
ADT08060R5	ADT08060R5	31.3in	23.43in	0.61in	14ga	2
ADT10060R5	ADT10060R5	39.17in	23.43in	0.61in	14ga	1
ADT10080R5	ADT10080R5	39.17in	31.3in	0.61in	14ga	1
ADT12060R5	ADT12060R5	47.05in	23.43in	0.61in	14ga	1
ADT12080R5	ADT12080R5	47.05in	31.3in	0.61in	14ga	1

## ADDITIONAL PRODUCT DETAILS

---

\* 3 point espagnolette locking. Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**