

Varistar CP Steel Door, Perforated With 1-Point Locking

Data Solutions



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

FEATURES

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP20

Material: Steel

Table 1/2

Catalog Number	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-006	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-007	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-008	52U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-013	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-014	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-015	52U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-408	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-409	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-410	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-411	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-412	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-413	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-414	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-415	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-507	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-508	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-509	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-510	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-511	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-512	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-513	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-514	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-515	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-516	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-517	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-518	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

Table 2/2

Catalog Number	Type	Works With
21630-006	Steel Door, Perforated	Varistar CP
21630-007	Steel Door, Perforated	Varistar CP
21630-008	Steel Door, Perforated	Varistar CP
21630-013	Steel Door, Perforated	Varistar CP
21630-014	Steel Door, Perforated	Varistar CP
21630-015	Steel Door, Perforated	Varistar CP
21630-408	Steel Door, Perforated	Varistar CP
21630-409	Steel Door, Perforated	Varistar CP
21630-410	Steel Door, Perforated	Varistar CP
21630-411	Steel Door, Perforated	Varistar CP
21630-412	Steel Door, Perforated	Varistar CP
21630-413	Steel Door, Perforated	Varistar CP

Catalog Number	Type	Works With
21630-414	Steel Door, Perforated	Varistar CP
21630-415	Steel Door, Perforated	Varistar CP
21630-507	Steel Door, Perforated	Varistar CP
21630-508	Steel Door, Perforated	Varistar CP
21630-509	Steel Door, Perforated	Varistar CP
21630-510	Steel Door, Perforated	Varistar CP
21630-511	Steel Door, Perforated	Varistar CP
21630-512	Steel Door, Perforated	Varistar CP
21630-513	Steel Door, Perforated	Varistar CP
21630-514	Steel Door, Perforated	Varistar CP
21630-515	Steel Door, Perforated	Varistar CP
21630-516	Steel Door, Perforated	Varistar CP
21630-517	Steel Door, Perforated	Varistar CP
21630-518	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE