

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Data Solutions



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Locking Type: 3-Point Locking

Product Type: Cabinet Door

Protection Rating: IP55

Material: Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-171	47U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-210	24U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-211	29U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-212	33U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-213	38U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-214	42U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-215	47U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-216	24U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-217	29U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-218	33U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-219	38U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-220	42U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

Table 2/2

Catalog Number	Type	Works With
21630-171	Steel Door	Varistar CP
21630-210	Steel Door	Varistar CP
21630-211	Steel Door	Varistar CP
21630-212	Steel Door	Varistar CP
21630-213	Steel Door	Varistar CP
21630-214	Steel Door	Varistar CP
21630-215	Steel Door	Varistar CP
21630-216	Steel Door	Varistar CP

Catalog Number	Type	Works With
21630-217	Steel Door	Varistar CP
21630-218	Steel Door	Varistar CP
21630-219	Steel Door	Varistar CP
21630-220	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE