

EuropacPRO 19" Subrack Kit for Backplane, Shielded

Power Utilities

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPECIFICATIONS

Product Type: Subrack/Chassis

Table 1/2						
Catalog Number	Rack Height	Package Quantity	For Mounting	EMC Gasket Type	Handle Included	Mounting
24563-142	3 U	1	Backplane	Textile	No	Rack
24563-143	3 U	1	Backplane	Textile	No	Rack
24563-144	3 U	1	Backplane	Textile	No	Rack
24563-145	3 U	1	Backplane	Textile	No	Rack
24563-146	3 U	1	Backplane	Textile	No	Rack
24563-442	6 U	1	Backplane	Textile	No	Rack
24563-443	6 U	1	Backplane	Textile	No	Rack
24563-444	6 U	1	Backplane	Textile	No	Rack
24563-445	6 U	1	Backplane	Textile	No	Rack
24563-446	6 U	1	Backplane	Textile	No	Rack

Table 2/2			
Catalog Number	Complies With	EMC Shielding	Rack Width
24563-142	IEC 60297-3-103	Yes	84 HP
24563-143	IEC 60297-3-103	Yes	84 HP
24563-144	IEC 60297-3-103	Yes	84 HP
24563-145	IEC 60297-3-103	Yes	84 HP
24563-146	IEC 60297-3-103	Yes	84 HP

Catalog Number	Complies With	EMC Shielding	Rack Width
24563-442	IEC 60297-3-103	Yes	84 HP
24563-443	IEC 60297-3-103	Yes	84 HP
24563-444	IEC 60297-3-103	Yes	84 HP
24563-445	IEC 60297-3-103	Yes	84 HP
24563-446	IEC 60297-3-103	Yes	84 HP

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE