

Front Panel, Anodized, Unshielded, Screw Assembly

Power Utilities

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, anodized

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-596	4 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized
30807-833	6 U	7 HP		Screw-on Front	Anodized	Anodized

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Material	Product Type	Type
30807-416	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-494	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-506	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Material	Product Type	Type
30807-596	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-764	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-771	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-776	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30808-067	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30810-432	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30818-741	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-481	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-482	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-483	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-484	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-485	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-487	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-496	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-501	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Material	Product Type	Type
30807-508	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-509	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-510	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-778	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-777	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-752	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-753	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-755	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-757	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-758	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-766	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-779	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-780	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
30807-833	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle

Table 3/3

Catalog Number	Certifications
----------------	----------------

30807-416	RoHS
30807-494	RoHS
30807-506	RoHS
30807-596	
30807-764	RoHS
30807-771	RoHS
30807-776	RoHS
30808-067	RoHS
30810-432	RoHS
30818-741	RoHS
30807-481	RoHS
30807-482	RoHS
30807-483	RoHS
30807-484	RoHS
30807-485	RoHS
30807-487	RoHS
30807-496	RoHS
30807-501	RoHS
30807-508	RoHS

30807-509	RoHS
30807-510	RoHS
30807-778	RoHS
30807-777	RoHS
30807-752	RoHS
30807-753	RoHS
30807-755	RoHS
30807-757	RoHS
30807-758	RoHS
30807-766	RoHS
30807-779	RoHS
30807-780	RoHS
30807-833	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE