

RatiopacPRO AIR 19" Rack Mount Case, Retrofittable Shielding With Handles

Power Utilities



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides advanced cooling capabilities and mounting brackets with handles for assembly into a 19" rack.

CERTIFICATIONS





FEATURES

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Retrofittable EMC shielding

Version with 19" mounting brackets with front handles, no visible screws

The case has 2 x 1/2 U clearances for ventilation beneath and above the board cage

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

Conforms with DIN EN 62368-1

SPECIFICATIONS

Table 1/2						
Catalog Number	Rack Height	Package Quantity	Front Frame Construction	Cooling Option	Complies With	EMC Shielding

24572-670	3 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-673	3 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-674	3 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-675	3 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-676	3 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-690	6 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-693	6 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-694	6 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)

24572-695	6 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)
24572-696	6 U	1	19" Mounting Brackets with Handles, Horizontal Rails	Yes	IEC 60297-3- 101, IEC 60297- 3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)

Table 2/2						
Catalog Number	Product Family	Product Type	Protection Rating	Rack Width	Туре	
24572-670	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-673	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-674	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-675	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-676	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-690	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-693	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-694	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-695	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	
24572-696	RatiopacPRO AIR	Case	IP20	84 HP	Case for Individual Electronic Components	

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE