

Varistar CP Cabinet Frame, Seismic

Power Utilities

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Shock and Vibration Tolerance	Color	Color Code	Complies With	Frame Material
20630-358	33 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-359	33 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-360	33 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-361	33 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-362	38 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-363	38 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-364	38 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel

CatalogNumber	Rack Height	Shock and Vibration Tolerance	Color	Color Code	Complies With	Frame Material
20630-365	38 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-366	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-367	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-368	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-369	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-370	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-371	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-372	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-373	42 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-374	47 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-375	47 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-376	47 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel
20630-377	47 U	5 g (force)	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Steel

Table 2/2

Catalog Number	Material	Product Type	Type	Works With
20630-358	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-359	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-360	Steel	Cabinet/Rack Frame	Seismic	Varistar CP

Catalog Number	Material	Product Type	Type	Works With
20630-361	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-362	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-363		Cabinet/Rack Frame	Seismic	Varistar CP
20630-364	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-365	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-366	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-367	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-368	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-369	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-370	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-371	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-372	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-373	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-374	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-375	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-376	Steel	Cabinet/Rack Frame	Seismic	Varistar CP
20630-377	Steel	Cabinet/Rack Frame	Seismic	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE