


# Telecom Grounding Busbar



## CERTIFICATIONS



## FEATURES

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

## SPECIFICATIONS

**Thickness (T):** 1/4"  
**Width (W):** 2"  
**Material:** Copper

Table 1/2


Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
TGBA12L06P	No	12"	9"	5/16"	6	7/16"

CatalogNumber	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number ofPairs	Hole Size 2 (HS2)
TGBA12L06PT	Yes	12"	9"	5/16"	6	7/16"
TGBA16L08P	No	15 1/2"	9"	5/16"	8	7/16"
TGBA16L08PT	Yes	15 1/2"	9"	5/16"	8	7/16"
TGBA18L10P	No	17 3/4"	9"	5/16"	10	7/16"
TGBA18L10PT	Yes	17 3/4"	9"	5/16"	10	7/16"
TGBA20L12P	No	20"	9"	5/16"	12	7/16"
TGBA20L12PT	Yes	20"	9"	5/16"	12	7/16"
TGBA24L14P	No	24"	18"	5/16"	14	7/16"
TGBA24L14PT	Yes	24"	18"	5/16"	14	7/16"
TGBA29L18P	No	29"	18"	5/16"	18	7/16"
TGBA29L18PT	Yes	29"	18"	5/16"	18	7/16"

Table 2/2				
Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA12L06P	3	1"	1 1/8"	5/8"
TGBA12L06PT	3	1"	1 1/8"	5/8"
TGBA16L08P	3	1"	1 1/8"	5/8"
TGBA16L08PT	3	1"	1 1/8"	5/8"
TGBA18L10P	3	1"	1 1/8"	5/8"

Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA18L10PT	3	1"	1 1/8"	5/8"
TGBA20L12P	3	1"	1 1/8"	5/8"
TGBA20L12PT	3	1"	1 1/8"	5/8"
TGBA24L14P	5	1"	1 1/8"	5/8"
TGBA24L14PT	5	1"	1 1/8"	5/8"
TGBA29L18P	5	1"	1 1/8"	5/8"
TGBA29L18PT	5	1"	1 1/8"	5/8"

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**