

# Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

## Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

### FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

### SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Locking Type	Material
21630-760	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel
21630-761	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel
21630-762	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel
21630-763	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel
21630-764	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel

CatalogNumber	Rack Height	Color	Color Code	Complies With	Locking Type	Material
21630-765	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	4-Point Locking	Steel
21630-766	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	5-Point Locking	Steel
21630-767	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	5-Point Locking	Steel

Table 2/2

Catalog Number	Product Type	Protection Rating	Type	Works With
21630-760	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-761	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-762	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-763	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-764	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-765	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-766	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-767	Cabinet Door	IP55	Steel Door, Plain	Varistar CP

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**