

Varistar CP Steel Door, Plain With 3-Point Locking, IP20

Power Utilities

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-104	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-105	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-106	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-107	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-108	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-109	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-432	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

CatalogNumber	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-433	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-434	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-435	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-436	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-437	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-438	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-439	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

Table 2/2

Catalog Number	Protection Rating	Type	Works With
21630-104	IP20	Steel Door	Varistar CP
21630-105	IP20	Steel Door	Varistar CP
21630-106	IP20	Steel Door	Varistar CP
21630-107	IP20	Steel Door	Varistar CP
21630-108	IP20	Steel Door	Varistar CP
21630-109	IP20	Steel Door	Varistar CP
21630-432	IP20	Steel Door	Varistar CP
21630-433	IP20	Steel Door	Varistar CP
21630-434	IP20	Steel Door	Varistar CP
21630-435	IP20	Steel Door	Varistar CP

Catalog Number	Protection Rating	Type	Works With
21630-436	IP20	Steel Door	Varistar CP
21630-437	IP20	Steel Door	Varistar CP
21630-438	IP20	Steel Door	Varistar CP
21630-439	IP20	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE