

Pyropak Termination Kit

nVent PYROTENAX Pyropak Termination Kit is a range of mineral insulated (MI) termination kits for 8 AWG and 10 AWG single conductor and all multiconductor copper sheathed cables. The cable end is sealed using either a mastic or epoxy sealing compound, depending on the temperature rating required. Each kit contains enough material to terminate two cable ends. To reduce installation time, MI wiring cables can be supplied with factory terminated ends, using brass gland connectors and epoxy sealed cable ends.

FEATURES

Easy to use

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Max Operating Temperature: 221 °F
Voltage Rating: 600 V max

Table 1/1

Catalog Number	Tail Size	Suitable for Cable Type	Thread Size	Thread Type
PPK15	36 in	3/4-746	1-1/4"	NPT
PPK35	36 in	3/3-834	1-1/4"	NPT
PPK37	36 in	4/6-730	1-1/4"	NPT
PPK1	12 in	2/16-340	1/2"	NPT
PPK2	12 in	2/14-371	1/2"	NPT
PPK3	12 in	3/14-387	1/2"	NPT

Catalog Number	Tail Size	Suitable for Cable Type	Thread Size	Thread Type
PPK30	36 in	2/14-371	1/2"	NPT
PPK32	36 in	2/16-340	1/2"	NPT
PPK34	12 in	2/18-215T	1/2"	NPT
PPK4	12 in	2/12-402	1/2"	NPT
PPK5	36 in	2/12-402	1/2"	NPT
PPK6	12 in	2/18-324TS	1/2"	NPT
PPK31	12 in	2/16-246T	3/4"	NPT
PPK33	12 in	2/16-364TS	3/4"	NPT
PPK8	12 in	3/10-480	3/4"	NPT
PPK9	36 in	3/10-480	3/4"	NPT
PPK10	12 in	3/12-480	3/4"	NPT
PPK11	36 in	3/12-480	3/4"	NPT
PPK12	36 in	3/8-590	3/4"	NPT
PPK13	12 in	3/6-621	3/4"	NPT
PPK14	36 in	3/6-621	3/4"	NPT
PPK36	36 in	4/10-590	3/4"	NPT
PPK7	12 in	4/14-465	3/4"	NPT

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT