

TT1000 Water Sensing Cable, Modular



nVent RAYCHEM TraceTek TT1000-XX-PC are a range of fixed length water sensing cables with factory installed plastic connectors. Mainly used in commercial building applications, it is typically intended for leak detection under raised floors, in mechanical rooms and similar flat surface areas. It detects the presence of water at any point along its length. Installed with an alarm and locating module, the cable senses water leaks, triggers an alarm and pinpoints the location.

FEATURES

Advanced technology: rugged conductive polymer and fluoropolymer construction, resistant to corrosion and abrasion

Simple and fast to install: small, lightweight and flexible

Easy to design, fast drying, and reuseable

Distributed leak detection and location over a wide range of areas

Reliable and durable, 10 year product warranty available

SPECIFICATIONS

Outer Diameter:	0.236 in
Max Operating Temperature:	167 °F
Detection Method:	Raychem Conductive-Polymer Technology
Detection:	Water

Table 1/1

Catalog Number	Item Name	Length
017859-000	TT1000-7.5M/25FT-PC	25 ft
072827-000	TT1000-5M/17FT-PC	17 ft
391887-000	TT1000-3M/10FT-PC	10 ft
396807-000	TT1000-30M/100FT-PC	100 ft

Catalog Number	Item Name	Length
409271-000	TT1000-1M/3FT-PC	3 ft
805147-000	TT1000-15M/50FT-PC	50 ft
P000000702	TT1000-100M/330FT-PC	330 ft
P000000864	TT1000-25M/82FT-PC	82 ft
P000000873	TT1000-50M/165FT-PC	165 ft
P000001222	TT1000-6M/20FT-PC	20 ft
P000001223	TT1000-10M/33FT-PC	33 ft
P000001224	TT1000-12M/39FT-PC	39 ft
P000001225	TT1000-30M/98FT-PC	98 ft
P000001226	TT1000-45M/147FT-PC	147 ft

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT