

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICATIONS

Product Type: Assembly Kit

Finish: Zinc Plated

Table 1/2

Catalog Number	Package Quantity	Thread Size	Material	Product Family	Type	Works With
----------------	------------------	-------------	----------	----------------	------	------------

21190-095	4	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets
21120-196	4	M6	Steel		Mounting Kit, Grounding	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21100-435	8	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets
21120-215	32	M6	Steel		Mounting Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21101-809	50	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets
21120-214	50	M6	Steel		Mounting Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP

21120-198	50	M6	Steel		Mounting Kit, Grounding	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21101-810	100	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets
21120-216	100	M6	Steel		Mounting Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21120-213	4	M6	Steel		Mounting Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21120-199	100	M6	Steel		Mounting Kit, Grounding	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21120-197	32	M6	Steel		Mounting Kit, Grounding	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21190-435	32	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets

Table 2/2

Catalog Number	Certifications	Quick Ship
----------------	----------------	------------

21190-095	RoHS	No
21120-196		No
21100-435	RoHS	No
21120-215		No
21101-809	RoHS	No
21120-214		No
21120-198		No
21101-810	RoHS	No
21120-216		No
21120-213		No
21120-199		No
21120-197		No
21190-435	RoHS	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE