

# 19" Front Panel With Holes for Handles



Define the device fronts and side inss with Schroff 19" front panels. Schroff 19" front panels have additional holes for mounting of handles and are available in 1 U to 6 U demensions.

### **CERTIFICATIONS**



# **FEATURES**

19" front panels have additional holes for mounting of handles

Front Panel

# **SPECIFICATIONS**

**Product Type:** 

Rack Width: 95HP

Material: Aluminum

Accessory Type: Front panel


Table 1/2							
Catalog Number	Rack Height	Handle Type	Finish	Mounting	Package Quantity	Front Finish	
30219-161	1U	Front Handle	Anodized	Screw-on Front	1	Anodized	
40304-050	1U	Front Handle	Anodized	Screw-on Front	1	Anodized	
30219-162	2U	Front Handle	Anodized	Screw-on Front	1	Anodized	

CatalogNumber	Rack Height	Handle Type	Finish	Mounting	Package Quantity	Front Finish
40304-051	2U	Front Handle	Anodized	Screw-on Front	1	Anodized
30219-163	3U	Front Handle	Anodized	Screw-on Front	1	Anodized
30219-164	4U	Front Handle	Anodized	Screw-on Front	1	Anodized
40304-052	3U	Front Handle	Anodized	Screw-on Front	1	Anodized
30219-165	5U	Front Handle	Anodized	Screw-on Front	1	Anodized
40304-053	4U	Front Handle	Anodized	Screw-on Front	1	Anodized
30219-166	6U	Front Handle	Anodized	Screw-on Front	1	Anodized
40304-054	5U	Front Handle	Anodized	Screw-on Front	1	Anodized
40304-055	6U	Front Handle	Anodized	Screw-on Front	1	Anodized

Table 2/2						
<b>Catalog Number</b>	Rear Finish	Treated Edges	EMC Shielding	Туре	Quick Ship	
30219-161	Anodized	No	No	19" Front Panel	No	
40304-050	Anodized	Yes	No	19" Front Panel	No	
30219-162	Anodized	No	No	19" Front Panel	No	
40304-051	Anodized	Yes	No	19" Front Panel	No	
30219-163	Anodized	No	No	19" Front Panel	No	
30219-164	Anodized	No	No	19" Front Panel	No	
40304-052	Anodized	Yes	No	19" Front Panel	No	
30219-165	Anodized	No	No	19" Front Panel	No	

Catalog Number	Rear Finish	Treated Edges	EMC Shielding	Туре	Quick Ship
40304-053	Anodized	Yes	No	19" Front Panel	No
30219-166	Anodized	No	No	19" Front Panel	No
40304-054	Anodized	Yes	No	19" Front Panel	No
40304-055	Anodized	Yes	No	19" Front Panel	No

## **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

# Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE