

# **AMC Front Panel With Pull Handle**



AdvancedMC Front Panel including EMC gasket for AMC.0 Rev. 2.0 Modules.

#### **CERTIFICATIONS**



#### **FEATURES**

In accordance with AMC.0 R2.0 specification

Front panel for pull-handle mechanism (with cut-outs for light pipe)

For the use together with the AMC Pull-handle mechanism, AMC.0 R2.0


# **SPECIFICATIONS**

Accessory Type: Front panel Product Type: Front Panel

Table 1/2							
Catalog Number	Rack Width	Design Feature	Material	Finish	Package Quantity	Front Finish	
30849-682	6НР	Full-Size	Aluminum	Passivated	1	Raw	
30849-670	4HP		Aluminum	Passivated	1	Raw	
30849-694	6НР	Full-Size	Aluminum	Passivated	1	Raw	

CatalogNumber	Rack Width	Design Feature	Material	Finish	Package Quantity	Front Finish
30849-403	4HP	Mid-Size	Stainless Steel		1	Raw
30849-404	6НР	Full-Size	Stainless Steel		1	Raw
30849-406	4HP	Mid-Size	Stainless Steel		1	Raw
30849-407	6НР	Full-Size	Stainless Steel		1	Raw
30849-402	3HP	Compact	Stainless Steel		1	Raw
30849-658	4HP	Mid-Size	Aluminum	Passivated	1	Raw

Table 2/2						
Catalog Number	Rear Finish	Quick Ship				
30849-682	Raw	No				
30849-670	Raw	No				
30849-694	Raw	No				
30849-403	Raw	No				
30849-404	Raw	No				
30849-406	Raw	No				
30849-407	Raw	No				
30849-402	Raw	No				
30849-658	Raw	No				



# **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**