

# Easy Swap Adaptor Plenums for Air Conditioners



When existing air conditioners are damaged or have reached end-of-life, Easy Swap Adaptor Plenums provide a quick and easy means for attaching a new nVent HOFFMAN air conditioners to the cutout left on the enclosure.

## INDUSTRY STANDARDS

---

Maintains NEMA Type 12 rating when properly installed on a Type 12 enclosure.

NEMA Type 12

IP 54

## FEATURES

---

No modification of the enclosure required - designed to match the enclosure cut-out and mounting holes of the air conditioner being replaced

Plenum design allows for optimum air flow (vs. a flat plate that can block the air intake and air outtake left by the older air conditioner)

Gasket included

## SPECIFICATIONS

**Color:** Light Gray

**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PL17N21	36416	20.87in	12in	1.5in	Mild Steel	Powder Coated
PL17N21SS	36417	20.87in	12in	1.5in	Stainless Steel 316L	Brushed #4
PLCR23N21	36412	23in	10in	1.5in	Mild Steel	Powder Coated
PLCR23N21SS	36411	23in	10in	1.5in	Stainless Steel 316L	Brushed #4
PLHC52G57	26301	57.6in	22.97in	1.5in	Mild Steel	Powder Coated
PLHC52T53	26302	52.85in	23in	1.5in	Mild Steel	Powder Coated
PLKG28	26582	36.87in	19.13in	1.5in	Mild Steel	Powder Coated
PLKG52	26581	52.56in	19.13in	1.5in	Mild Steel	Powder Coated
PLKTN17	26568	19in	12in	1.5in	Mild Steel	Powder Coated
PLKTN28	26505	33.25in	12.25in	1.5in	Mild Steel	Powder Coated
PLM13N16	36414	17.65in	14.25in	2.62in	Mild Steel	Powder Coated
PLM13N17	26556	17.65in	14.25in	1.5in	Mild Steel	Powder Coated
PLM28G28	26294	28.5in	17in	1.5in	Mild Steel	Powder Coated
PLM28N17	26557	28.5in	17in	1.5in	Mild Steel	Powder Coated
PLM33N28	26296	34.31in	12in	1.5in	Mild Steel	Powder Coated
PLM36N36	26297	38.75in	15in	1.5in	Mild Steel	Powder Coated
PLM52G52	26298	52.56in	17.03in	1.5in	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PLPN36	26537	36.5in	12in	1.5in	Mild Steel	Powder Coated
PLR1N17	26066	21.65in	13in	1.5in	Mild Steel	Powder Coated
PLR2G28	26504	37.4in	16.97in	1.5in	Mild Steel	Powder Coated
PLR2N17	26067	21.65in	12in	1.5in	Mild Steel	Powder Coated
PLRG28	21496	37.4in	16.97in	1.5in	Mild Steel	Powder Coated
PLRG52	19862	61.13in	17.13in	1.5in	Mild Steel	Powder Coated
PLRG57	26073	61.13in	20.88in	1.5in	Mild Steel	Powder Coated
PLRN28	26068	29in	11.5in	1.5in	Mild Steel	Powder Coated
PLRN36	26538	38in	15.75in	1.5in	Mild Steel	Powder Coated
PLT29G28	26295	28.5in	17in	1.5in	Mild Steel	Powder Coated

## ADDITIONAL PRODUCT DETAILS

To quickly identify the correct air conditioner and plenum download the spec sheet from the Downloads tab or download the Easy Swap app from Apple App or Google play stores

Please contact Customer Service for support in finding an appropriate cross for older HOFFMAN/Mclean models not shown above.

Prior to ordering, ensure Adaptor Plenum dimensions do not exceed available space on the enclosure mounting surface.

ISC is a registered trademark of ISC Sales, Inc.

Kooltronic is a registered trademark of Kooltronic, Inc.

Pfannenbergl is a registered trademark of Pfannenbergl Incorporated

Rittal is a registered trademark of Rittal Corporation

Adaptor Plenums for Rittal are not suitable for replacing partial-recessed or fully-recessed mounted air conditioners.

Thermal Edge is a registered trademark of Thermal Edge, Inc.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**