

Hazardous Location Hole Seals

Hazardous Location Hole Seals are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. Certified to be used on metallic, non-painted enclosures, these hole seals ensure a dust-, oil- and water-tight seal. Designed to seal extra pushbutton holes, conduit openings and knockout openings, these self-centering hole seals are easy to install.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12, 3R; File No. 42186

IECEX and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE

2 assemblies

ATEX Directive 94/9/EC

ATEX

Ex e IIC Gb

Ex tb IIIC Db IP 66

Sira 14ATEX3233U

IECEX

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEX SIR 14.0073U

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66



FEATURES

Secure sealing with silicon rubber gasket to protect against water and dust ingress in extreme temperature applications ranging from -55 C (-67 F) to 180 C (356 F)

Seal pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water

Easy installation in enclosure cutouts with self-centering hole seals

Hole seals are available in metric and english standard hole sizes

SPECIFICATIONS

Finish: Brushed
Material: Stainless Steel 316L

Table 1/1

Catalog Number	Article Number	Hole Diameter	Assembly Diameter	Thread Size	Quick Ship
EXAS250SS6	28788	2.952 – 3.051in	3.64in	M75	No
EXAS100SS6	28784	1.259 – 1.358in	1.89in	M32	No
EXAS150SS6	28786	1.968 – 2.066in	2.64in	M50	No
EXAS075SS6	28783	0.984 – 1.082in	1.71in	M25	No
EXAS050SS6	28782	0.787 – 0.885in	1.36in	M20	No
EXAS125SS6	28785	1.574 – 1.673in	2.33in	M40	No
EXAS200SS6	28787	2.48 – 2.578in	3.14in	M63	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE