

Mounting Plates Power Distribution, BMP



The steel mounting plate contributes to speeding up the assembly of the terminal box since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Steel mounting plate for terminal boxes.

Material: 2 mm galvanized steel.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 14ga
Finish: Galvanized
Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Panel Size	Enclosure Material
BMP1515	BMP1515	5.91in	5.91in	0.08in	4.92 x 4.72in	Mild Steel
BMP1530	BMP1530	5.91in	11.81in	0.08in	4.92 x 10.63in	Mild Steel
BMP2020	BMP2020	7.87in	7.87in	0.08in	6.89 x 6.69in	Mild Steel
BMP2030	BMP2030	7.87in	11.81in	0.08in	6.89 x 10.63in	Mild Steel
BMP2040	BMP2040	7.87in	15.75in	0.08in	6.89 x 14.57in	Mild Steel
BMP2050	BMP2050	7.87in	19.69in	0.08in	6.89 x 18.5in	Mild Steel
BMP2060	BMP2060	7.87in	23.62in	0.08in	7.09 x 22.44in	Mild Steel
BMP2080	BMP2080	7.87in	31.5in	0.08in	7.09 x 30.31in	Mild Steel
BMP3030	BMP3030	11.81in	11.81in	0.08in	10.83 x 10.63in	Mild Steel
BMP3040	BMP3040	11.81in	15.75in	0.08in	10.83 x 14.57in	Mild Steel
BMP3050	BMP3050	11.81in	19.69in	0.08in	10.83 x 18.5in	Mild Steel
BMP3060	BMP3060	11.81in	23.62in	0.08in	11.02 x 22.44in	Mild Steel
BMP4040	BMP4040	15.75in	15.75in	0.08in	14.76 x 14.57in	Mild Steel
BMP4060	BMP4060	15.75in	23.62in	0.08in	14.96 x 22.44in	Mild Steel
BMP4080	BMP4080	15.75in	31.5in	0.08in	14.96 x 30.31in	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE