

Panels for Free-Stand with Mounting Channel Two-Door



Panel for Free-Stand Single- and Dual-Access Two-Door Enclosures with Mounting Channel. Panels can be positioned anywhere along horizontal mounting channels (see Sections B-B for limitations). Half-length panels can be located in the upper or lower portion of the enclosure. Some assembly is required. Center support is furnished with each full-length or half-length panel for two-door enclosures. The center support attaches to the top and bottom mounting channels and can be positioned from front to back in the enclosure. The center support can be replaced with heavy duty panel supports to support panels when heavy equipment is installed.

FEATURES

Available in Full-Length and Half-Length

Plated mounting hardware is provided

SPECIFICATIONS

Material: Mild Steel

Table 1/1						
Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A60P48F1G	15022	48in	44in	Galvanized		11ga
A60P48F1	27610	48in	44in	Powder Coated	White	11ga
A72P48F2	27030	30.88in	44in	Powder Coated	White	11ga
A72P48F2G	15013	30.88in	44in	Galvanized		11ga
A72P48F1	27020	60in	44in	Powder Coated	White	11ga
A72P48F1G	15012	60in	44in	Galvanized		11ga
A90P48F2	27820	39.88in	44in	Powder Coated	White	11ga
A90P48F2G	15024	39.88in	44in	Galvanized		11ga
A72P60F1	27040	60in	56in	Powder Coated	White	11ga
A72P60F1G	15014	60in	56in	Galvanized		11ga
A72P60F2	27050	30.88in	56in	Powder Coated	White	11ga
A72P60F2G	15015	30.88in	56in	Galvanized		11ga
A72P72F1G	15016	60in	68in	Galvanized		11ga
A72P72F2G	15017	30.88in	68in	Galvanized		11ga
A72P72F1	27060	60in	68in	Powder Coated	White	11ga
A72P72F2	27070	30.88in	68in	Powder Coated	White	11ga
A90P72F2	27090	39.88in	68in	Powder Coated	White	11ga
A90P72F2G	15021	39.88in	68in	Galvanized		11ga

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72P60F1B	57083	60in	56in	Powder Coated	White	11ga
A72P72F1B	57052	60in	68in	Powder Coated	White	11ga
A90P48F1	27810	78in	44in	Powder Coated	White	11ga
A90P48F1G	15023	78in	44in	Galvanized		11ga
A90P72F1G	15018	78in	68in	Galvanized		11ga
A90P72F1	27080	78in	68in	Powder Coated	White	11ga
A90PM72F1B	57037	78in	68in	Powder Coated	White	11ga

ADDITIONAL PRODUCT DETAILS

Catalog numbers with B suffix include two painted panels bolted together, with top and bottom stiffeners for additional support.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE