

Partial Subpanel



Partial Subpanels have flanges on four sides. Panels can be positioned vertically in 25-mm increments and also can be positioned at any depth in 25-mm increments using the optional grid straps. All necessary mounting hardware is included.

FEATURES

12 gauge steel; conductive or white painted finish

All necessary mounting hardware is included

Partial Subpanels have flanges on four sides for added strength.

Panels can be positioned vertically in 25-mm increments, but also can be positioned at any depth in 25-mm increments using depth-mounted grid straps for securing (sold separately)

SPECIFICATIONS

Thickness: 12ga

Table 1/1

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
PPP86	99250	Mild Steel	White	Powder Coated	No
PPP46	99210	Mild Steel	White	Powder Coated	No
PPP116	99350	Mild Steel	White	Powder Coated	No
PPP96	99290	Mild Steel	White	Powder Coated	No
PPP96G	14482	Mild Steel		Galvanized	No
PPP86G	15102	Mild Steel		Galvanized	No
PPP106	99330	Mild Steel	White	Powder Coated	No
PPP46G	15096	Mild Steel		Galvanized	No
PPP116G	15112	Mild Steel		Galvanized	No
PPP106G	15108	Mild Steel		Galvanized	No
PPP48G	15098	Mild Steel		Galvanized	No
PPP88	99270	Mild Steel	White	Powder Coated	No
PPP108	99340	Mild Steel	White	Powder Coated	No
PPP98G	14483	Mild Steel		Galvanized	No
PPP48	99230	Mild Steel	White	Powder Coated	No
PPP98	99310	Mild Steel	White	Powder Coated	No
PPP88G	15104	Mild Steel		Galvanized	No
PPP108G	15111	Mild Steel		Galvanized	No

Catalog Number	Article Number	Material	Color	Finish	Quick Ship
PPP910	99320	Mild Steel	White	Powder Coated	No
PPP910G	15107	Mild Steel		Galvanized	No
PPP810	99280	Mild Steel	White	Powder Coated	No
PPP47	99220	Mild Steel	White	Powder Coated	No
PPP87	99260	Mild Steel	White	Powder Coated	No
PPP97	99300	Mild Steel	White	Powder Coated	No
PPP47G	15097	Mild Steel		Galvanized	No
PPP97G	15106	Mild Steel		Galvanized	No
PPP412	99240	Mild Steel	White	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE