

# **EuropacPRO Advanced EMC Plus, Dual Mesh Top and Bottom Covers, Screwed to Side Panel**



A cover plate is used for electromagnetic shielding and as mechanical protection. The cover can be screwed onto the side panel.

### **FEATURES**

Dual mesh top and bottom covers with EMC and airflow optimized perforation, for highest RF-shielding requirements

Fulfills the requirements of the fire safety standard EN 62368-1

For PCBs with standard formats

Cover plate for bolting to the side panel

Suitable for use with all horizontal rails, besides Rugged

### **SPECIFICATIONS**

Material:AluminumProduct Type:Cover PlateProduct Family:EuropacPROFinish:PassivatedType:PerforatedWorks With:Subracks

Table 1/1						
Catalog Number	Package Quantity	Rack Width	Package Unit	Quick Ship		
24563-770	2	84HP	Pair	No		
24563-771	2	84HP	Pair	No		

Catalog Number	Package Quantity	Rack Width	Package Unit	Quick Ship
24563-772	2	84HP	Pair	No
24563-780	2	84HP	Pair	No
24563-774	2	84HP	Pair	No
24563-781	2	84HP	Pair	No
24563-773	2	84HP	Pair	No
24563-775	2	84HP	Pair	No
24563-776	2	84HP	Pair	No
24563-777	2	84HP	Pair	No
24563-782	2	84HP	Pair	No
24563-783	2	84HP	Pair	No
24563-784	2	84HP	Pair	No
24563-790	2	84HP	Pair	No
24563-791	2	84HP	Pair	No
24563-792	2	84HP	Pair	No
24563-793	2	84HP	Pair	No

# WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE